

LOCTITE**Thread sealant yarn, 160 m, Manufacturer ID: 55**

Order data

Order number	083312 55
GTIN	4002872013986
Item class	04L

Description

Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Non-curing thread yarn, seals instantly, DVGW / KTW, WRC-approved.

Application:

Thread sealant yarn for plastics and metal in heating systems and plumbing applications.

Note:

Before applying sealant, clean the threads with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Manufacturer's designation	LOCTITE 55
for imperial thread size	4 in
for thread size M to	M110

Operating temperature range	-55 - 130 °C
Working life after date of manufacture	59 mo
Suitable for material	Plastic
Suitable for material	Metal
Length	160 m
Colour	white
Storage temperature	8 - 21 °C
Chemical basis	PA multifilament
Characteristics	no hardening
Strength class	low strength
Product name attribute	160 m
Type of product	Sealing strip