



Side lock arbor, SK 50, Clamping range \varnothing D1: 32mm



Order data

Order number	302440 32
GTIN	4250122600428
Item class	36E

Description

Version:

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

Spare clamping screw No. 30 9900	32
Thread M	M24
Overhang dimension A	80 mm
Clamping \varnothing D ₁	32 mm
Overall length L	207 mm
External \varnothing D	72 mm
Adapter	SK 50
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Pull stud 45°sealed suitable for steep tapers 50	308760 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull studForm A suitable for steep tapers 50	308600 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Spare clamping screw for chucks with clamping Ø D1 32 mm	309900 32