



LED-EX torch with batteries, Type: 2ELED



Order data

Order number	081522 2ELED
GTIN	032705133417
Item class	08C

Description

Version:

Explosion-proof torch, tested to the applicable ATEX guidelines.

High-performance inspection lamp, shock-resistant, dust-proof and waterproof.

Powerful LED pen lamp with pocket clip. Centre-reinforced beam, 6500K. Lightweight, fits into any tool bag and holds onto any jacket pocket. Switch at rear. With fibre optic attachment ideal for illuminating confined spaces that are difficult to access.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Illumination	40 lm
ATEX zone	Zone 1
ATEX zone	Zone 21
Battery type	Micro, AAA
Number of batteries contained	2
Colour of housing	yellow
Illumination time	3 h
Head Ø	22 mm
Weight	55 g
IP Index of Protection	IP 67

Overall length	132 mm
Tool properties	Suitable for EX areas
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Fibre optic attachment for pin-point illumination Type 2ELED	081528 2ELED
Alkaline-manganese batteries International size LR3	081554 LR3