



LED-EX torch with batteries, Type: 2ELED



Order data

Order number	081522 2ELED
GTIN	32705133417
Item class	08C

Description

Version:

Explosion-proof torch, tested to the applicable ATEX guidelines.

Special torches with **impact resistant** and **waterproof** ABS casing.

Powerful LED pen torch of the latest generation with pocket clip and switch at rear.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

IP Index of Protection: IP 67

ATEX zone: Zone 1

ATEX zone: Zone 21

Illumination: 35 lm

Working life: 3 h

Number of batteries contained: 2

Battery type: Micro, AAA

Technical description

Illumination	35 lm
ATEX zone	Zone 1
ATEX zone	Zone 21
Battery type	Micro, AAA
Number of batteries contained	2
Colour of housing	yellow

Working life	3 h
Head Ø	22 mm
Weight	53 g
IP Index of Protection	IP 67
Overall length	132 mm
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline manganese battery set International size LR3	081558 LR3
Alkaline-manganese batteries International size LR3	081556 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline manganese battery set International size LR3	081557 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Fibre optic attachment for pin-point illumination Type 2ELED	081528 2ELED
Alkaline-manganese batteries International size LR3	081554 LR3