



Data logger with Bluetooth® wireless technology, Type: 174T



Order data

Order number	474203 174T
GTIN	4029547027789
Item class	47B

Description

Version:

Handy data logger with display. Internal memory for 16,000 measurement values. High data security, even when the battery is flat. Measurement interval adjustable between 1 min. and 24 h. Battery life > 1 year (measurement interval 15 min., 25 °C). Time-saving and intuitive data read-outs via USB-C. Professional software with Excel export function for programming the logger and analysing data as well as data logging in PDF format.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Includes wall bracket, 2 batteries No. 081560 size CR2032, calibration certificate.

Technical description

Error limit temperature	±0.5 °C
Calibration	I9
IP Index of Protection	IP 65

Data sheet

Power supply	Battery-powered
Width	38 mm
Length	60 mm
Height	18.5 mm
#Article no of the battery / rechargeable battery fitted	081560 CR2032
#Number of batteries contained	2
Temperature measurement range	-30 - 70 °C
Interface	Bluetooth® interface
Device memory	16000 measured values
Type of product	Data logger

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/474203-174T>