

**Side lock arbor, SK 40, Clamping range \varnothing D1: 20mm****Order data**

Order number	302420 20
GTIN	4250122600299
Item class	36E

Description**Version:**

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

Overall length L	156 mm
Overhang dimension A	63 mm
Spare clamping screw No. 30 9900	20
Clamping \varnothing D ₁	20 mm
Thread M	M16
External \varnothing D	52 mm
Adapter	SK 40
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studsealed suitable for steep tapers 40	308660 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40

Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Spare clamping screw for chucks with clamping Ø D1 20 mm	309900 20