



Drill/driver, cordless drill/driver



Order data

Order number	074800 ISR18V30P
GTIN	4053423254853
Item class	03B

Description

Version:

Consistent, reliable and affordable 18V smart solution for industrial assembly lines.

- **Precision coupling: No oversteer when a set torque is reached. (Reduces coupling wear).**
- **Industrial ergonomics: Extreme compactness for high flexibility. Optimized handle size and light weight for industrial mounting.**

Note:

See No. 073851 – No. 073866 for suitable batteries and chargers.

Technical description

Battery voltage	18 V
Power supply	Battery-powered
No load speed	0 - 1400 min ⁻¹
Weight	0.7 kg
Type of rechargeable battery	Lithium-ion
typical application	Heavy Duty

Data sheet

Manufacturer's designation	ISR 18V-30 P
maximum vibration to EN	$<2.5 \text{ m/s}^2$
Number of rechargeable batteries contained	0
Tool arbor drive profile	Quick-clamping chuck
maximum torque	30 Nm