



## Impact wrench 18 V, cordless impact wrench



### Order data

Order number	074052 GDS18750C
GTIN	4059952655147
Item class	03B

### Description

#### Version:

Cordless impact wrench / impact driver.

· **Reversible.**

· **Battery charge display.**

Powerful 1/2" cordless impact screwdriver combines performance with a compact design.

· **Break-away torque of 1000 Nm combined with a head length of only 156 mm.**

· **Ideal for metal workshops/locksmiths, industrial metalworking, vehicle maintenance and construction.**

#### Supplied with:

Supplied with 2× Li-ion batteries, charger, L-BOXX

#### Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

### Technical description

Battery capacity	8 Ah
Power supply	Battery-powered
Packaging	Modular case (L-Boxx)

## Data sheet

Manufacturer's designation	GDS 18V-750 C
suitable battery - supplier / battery type / voltage	Bosch 18 V
maximum vibration to EN	13.5 m/s <sup>2</sup>
Weight	2.1 kg
Tool arbor drive profile	External square drive
typical application	Heavy Duty
maximum speed 2nd speed	3000 min <sup>-1</sup>
Battery voltage	18 V
Number of impacts	0 - 3000 min <sup>-1</sup>
maximum speed 1st speed	1500 min <sup>-1</sup>
Tool arbor size	1/2 in
Number of rechargeable batteries contained	2
maximum torque hard	750 Nm
Type of rechargeable battery	Lithium-ion
Type of product	Impact wrench