



Impact wrench 18 V, cordless impact wrench



Order data

Order number	074052 GDS1600HC
GTIN	4053423246377
Item class	03B

Description

Version:

Cordless impact wrench / impact driver.

- **Reversible.**
- **Battery charge display.**

Exceptional cable-free performance: 3/4" impact screwdriver with high traction power thanks to BITURBO brushless technology.

- **Strong impact screwdriver with a tightening torque of 1,600 Nm and break-away torque of 2,200 Nm.**
- **Auto Bolt Release (ABR) mode ensures convenient handling by preventing metal bolts or union nuts from falling off and being lost.**

Supplied with:

Supplied with 2× Li-ion batteries, charger, L-BOXX

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Technical description

Packaging	Modular case (L-Boxx)
-----------	-----------------------

Data sheet

Power supply	Battery-powered
maximum speed 1st speed	800 min ⁻¹
Tool arbor drive profile	External square drive
Battery capacity	8 Ah
maximum speed 2nd speed	1750 min ⁻¹
Weight	3.2 kg
typical application	Heavy Duty
Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Bosch 18 V
Number of rechargeable batteries contained	2
Manufacturer's designation	GDS 18V-1600HC
maximum vibration to EN	14 m/s ²
Number of impacts	0 - 2350 min ⁻¹
maximum torque hard	1600 Nm
Tool arbor size	3/4 in
Battery voltage	18 V
Type of product	Impact wrench