



Cordless angle grinder GWS, Type: 18V-8



Order data

Order number	077120 18V-8
GTIN	4053423323801
Item class	03C

Description

Version:

Extremely powerful 18 V cordless angle grinder in compact design.

Note:

See No. 073851 – 073866 for suitable rechargeable batteries and chargers.

Technical description

Kick-back stop	yes
Battery voltage	18 V
maximum cutting depth	34 mm
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
maximum speed	11000 min ⁻¹
Power supply	Battery-powered
Weight	2.3 kg
Soft start	yes
maximum vibration to EN	7 m/s ²

Data sheet

Overload protection	yes
Manufacturer's designation	GWS 18V-8
Dead man's circuit	no
Restart block	yes
maximum disc Ø	125 mm
Type of product	Angle grinder