

**Electrical angle grinder GWS, for 125 mm discs Ø, with restart inhibit****Order data**

Order number	077109 7-115E
GTIN	3165140823739
Item class	03C

Description**Version:**

720 watt 115 mm angle grinder with small handle circumference, offers optimised ergonomics for low-fatigue working.

· **Speed preselection enables a wide range of applications.**

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Technical description

Power supply	Mains-powered
Weight	1.9 kg
Power consumption	720 W
Restart block	yes
maximum cutting depth	28 mm
Speed range	2800 - 11000 min ⁻¹
maximum vibration to EN	6.5 m/s ²
Mains frequency	50 Hz
Manufacturer's designation	GWS 7-115E

Data sheet

maximum disc Ø	115 mm
Nominal voltage	230 V
Type of product	Angle grinder