



Safety helmet uvex pronamic B-WR, Colour: YELLOW



Order data

Order number	097706 YELLOW
GTIN	4031101960098
Item class	04U

Description

Version:

Pronamic stands for optimum protection (**pro**tection) and dynamism (**dynamic**): Light-weight helmet shell made of HDPE (High Density Polyethylene) with **three ventilation openings with variable adjustment options** for maximum ventilation. The optimised headband geometry and the large neck support ensure an extremely comfortable fit. The adapter system allows it to be combined with visors, helmet ear defenders and helmet lamps. **Resistant to low temperatures down to -30°C** and protection against splashes of liquid metal (MM).

- **6-point strap attachment**
- **30 mm Euro slot mounting**
- **Synthetic leather sweatband**
- **Straight form**
- **With rotary catch and large neck support**

Application:

Industry, building trade, installation work.

Standard:

DIN EN 397

Technical description

Weight	406 g
--------	-------

Data sheet

Width adjustment	Rotary closure
Series	uvex pronamic
Colour	yellow
Size	51 - 65 cm
Helmet characteristics	Beskyttelsesegenskab indtil -30°C
Helmet characteristics	Protection against liquid metal spraying out
Material of helmet shell	HDPE
Standard	DIN EN 397
Type of product	Safety helmet