

Garant**Mini burr GARANT Master Uni – medium, Carbide, Type: M0613****Order data**

Order number	546906 M0613
GTIN	4069515035996
Item class	51D

Description**Version:**

Carbide mini burr with shank Ø 3 mm.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shank Ø	3 mm
Head length	13 mm
Head Ø	6 mm
Overall length	43 mm
Shape description	pointed cone
Series	Master Uni
Tool material	Carbide
Long shank	no
Type of product	Burr

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Alu Mg	suitable only under restricted conditions
Steel < 900 N/mm ²	suitable
Steel < 1400 N/mm ²	suitable
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable
INOX	suitable
Ti	suitable
GG(G)	suitable
Uni	suitable