

**DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL10****Order data**

Order number	220377 DL10
GTIN	4034221193698
Item class	10N

Description**Version:**

Technically optimised.

Note:

Special dimensions available on request.

Technical description

Shank Ø D _s	10 mm
Recommended torque	20 Nm
L ₂	37.5 mm
Ø D ₂	9.6 mm
DUO-LOCK interface	DL10
Overall length L	77.5 mm
Through-coolant	yes
Type of product	Arbor for threaded copy milling cutter