

**DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL16****Order data**

Order number	220377 DL16
GTIN	4034221193674
Item class	10N

Description**Version:**

Technically optimised.

Note:

Special dimensions available on request.

Technical description

Overall length L	108 mm
L ₂	60 mm
Ø D ₂	15.5 mm
DUO-LOCK interface	DL16
Recommended torque	60 Nm
Shank Ø D _s	16 mm
Through-coolant	yes
Type of product	Arbor for threaded copy milling cutter