

**DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL12****Order data**

Order number	220377 DL12
GTIN	4034221193681
Item class	10N

Description**Version:**

Technically optimised.

Note:

Special dimensions available on request.

Technical description

DUO-LOCK interface	DL12
Ø D ₂	11.5 mm
Shank Ø D _s	12 mm
L ₂	45 mm
Overall length L	93 mm
Recommended torque	30 Nm
Through-coolant	yes
Type of product	Arbor for threaded copy milling cutter