

**DUO-LOCK extension, cylindrical, solid carbide Plain shank, DUO-LOCK interface: DL20****Order data**

Order number	220377 DL20
GTIN	4034221193667
Item class	10N

Description**Version:**

Technically optimised.

Note:

Special dimensions available on request.

Technical description

DUO-LOCK interface	DL20
L ₂	75 mm
Recommended torque	80 Nm
Overall length L	125 mm
Ø D ₂	19.3 mm
Shank Ø D _s	20 mm
Through-coolant	yes
Type of product	Arbor for threaded copy milling cutter