

**Cordless circular saw, Type: M18FCS66GR****Order data**

Order number	078207 M18FCS66GR
GTIN	4058546483630
Item class	03L

Description**Version:**

Powerful **M18 FUEL™ cordless hand-held circular saw** maintains the 6,000 rpm throughout the entire cut, thanks to the new FORGE™ rechargeable battery.

- **An inclination angle of up to 50° is possible.**
- **Built-in dust blower keeps the cutting line clear.**

Supplied with:

Includes rechargeable battery, charger, transport case.

Note:

Suitable spare rechargeable batteries and chargers can be found as from No. 073801 – 073840.
For a suitable circular saw blade see from No. 584075.

Technical description

Battery capacity	12 Ah
Saw blade Ø	190 mm
maximum cutting depth 90°	68 mm
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Weight	3 kg

Data sheet

Manufacturer's designation	M18FCS66GR3-121C
Saw blade bore Ø	20 mm
Packaging	Modular case (HD=Heavy Duty)
Version	Hand-held circular saw
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Power supply	Rechargeable battery-powered
maximum vibration to EN	$< 2.5 \text{ m/s}^2$
maximum speed	6000 min^{-1}
Type of product	Saw

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/078207-M18FCS66GR>