



Impact wrench 18 V, cordless impact wrench



Order data

Order number	074010 M18ONEFHIW
GTIN	4058546564186
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. The **1 inch 18 V cordless impact wrench FUEL™** delivers up to 2033 Nm torque from a compact tool and needs neither a cable nor compressed air to do it. Integral impact rate adjustment increases the reproducible results for the chosen torque setting. With new **Forge™** 8.0 Ah rechargeable battery.

Supplied with:

Includes 2× M18 Forge™ 8 Ah, charger, HD box.

Note:

See No. 073801 – No. 073840 for suitable batteries and chargers.

Technical description

Data sheet

maximum torque 4th setting	2033 Nm
Number of impacts 3rd stage	0 - 2100 min ⁻¹
maximum screw Ø (8.8 - 12.9)	M42
App link	OneKey
Tool arbor drive profile	External square drive
Tool arbor size	1 in
Manufacturer's designation	M180NEFHI-WF1-802X
Number of impacts 2nd stage	0 - 1650 min ⁻¹
Battery capacity	8 Ah
maximum torque 3rd step	1800 Nm
Weight	5.9 kg
Power supply	Battery-powered
Number of impacts 1st stage	0 - 1350 min ⁻¹
typical application	Heavy Duty
Packaging	Modular case (HD=Heavy Duty)
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Battery voltage	18 V
Number of impacts 4th setting	0 - 2500 min ⁻¹
Number of rechargeable batteries contained	2
maximum torque 1st step	530 Nm
Type of rechargeable battery	Lithium-ion
maximum torque 2nd step	1020 Nm
Type of product	Impact wrench