

Garant**GARANT Master Mute boring bar shank vibration damping, Shank Ø / overall length L: 20/200****Order data**

Order number	265076 20/200
GTIN	4069515037358
Item class	29E

Description**Version:****With modular interface, suitable for systems from other manufacturers (e.g. Iscar).****Supplied with:**

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S! $D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3$.
 Usable length = overall length L minus clamping length (recommended = $3 \times D$). Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

recommended clamping length	60 mm
Shank Ø	20 mm
Overall length L	200 mm
non-clamping range S	84 mm
Assembly bolt set	269026 1
Version	Steel
Number of coolant channels	3
Connection thread	G1/4
Series	Master Mute
Vibration	damped

Through-coolant	yes
Type of product	Boring bar shanks

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265076-20/200>