

**Garant****GARANT Master Mute boring bar shank vibration damping, Shank Ø / overall length L: 25/330****Order data**

|              |               |
|--------------|---------------|
| Order number | 265076 25/330 |
| GTIN         | 4069515037396 |
| Item class   | 29E           |

**Description****Version:****With modular interface, suitable for systems from other manufacturers (e.g. Iscar).****Supplied with:**

Reducing adaptor for coolant connection.

**Note:**Do not clamp on the area marked S!  $D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3$ .Usable length = overall length L minus clamping length (recommended =  $3 \times D$ ). Use **only with internal cooling** (temperature resistance of up to max. 100°C).**Technical description**

|                             |             |
|-----------------------------|-------------|
| Assembly bolt set           | 269026 4    |
| non-clamping range S        | 125 mm      |
| Overall length L            | 330 mm      |
| recommended clamping length | 75 mm       |
| Shank Ø                     | 25 mm       |
| Version                     | Steel       |
| Number of coolant channels  | 3           |
| Connection thread           | G1/4        |
| Series                      | Master Mute |
| Vibration                   | damped      |

|                 |                   |
|-----------------|-------------------|
| Through-coolant | yes               |
| Type of product | Boring bar shanks |

**Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/265076-25/330>