



GARANT Master Mute boring bar shank vibration damping, Shank Ø / overall length L: 60/628



Order data

Order number	265076 60/628
GTIN	4069515037501
Item class	29E

Description

Version:

With modular interface, suitable for systems from other manufacturers (e.g. Iscar).

Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S! $D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3$.
Usable length = overall length L minus clamping length (recommended = $3 \times D$). Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

recommended clamping length	180 mm
Centre offset H base body	10 mm
Overall length L	628 mm
Assembly bolt set	269026 3
Shank Ø	60 mm
non-clamping range S	230 mm
Version	Steel
Number of coolant channels	1
Connection thread	G3/4
Series	Master Mute

Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265076-60/628>