



ER collet chuck, SK 40, for ER collet size: 32



Order data

Order number	302465 32
GTIN	4250122600107
Item class	36E

Description

Application:

For clamping tools with plain shank in ER / ESX collets to ISO 15488-B.

Optional extras:

ER collets No. 308981 – 309040, ER sets No. 309024 – 309320, ER clamping wrenches No. 309680 – 309740.

Technical description

Overhang dimension A	50 mm
for ER collets	32
Thread M	M16
Clamping range	2 - 20 mm
Spare ER clamping nut	32
External Ø D	50 mm
Adapter	SK 40
Arbor standard	DIN 2080
Concentricity	≤ 3 µm
Type of product	Collet chuck

Accessories

ER colletwith seal and spray nozzles Nominal clamping Ø d 8 mm	309002 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 17 mm	309002 17
ER colletwith seal Nominal clamping Ø d 16 mm	308986 16
ER collet Nominal clamping Ø d 4 mm	309000 4
ER collet Nominal clamping Ø d 3 mm	309000 3
ER collet Nominal clamping Ø d 3 mm	308981 3
ER collet set 18 pieces 3–20 mm	309024
ER collet Nominal clamping Ø d 9 mm	308981 9
ER collet Nominal clamping Ø d 6 mm	308981 6
ER collet Nominal clamping Ø d 20 mm	308981 20
ER colletwith seal Nominal clamping Ø d 10 mm	308986 10
ER colletwith seal Nominal clamping Ø d 4 mm	308986 4
ER colletwith seal and spray nozzles Nominal clamping Ø d 19 mm	309002 19
ER colletwith seal and spray nozzles Nominal clamping Ø d 12 mm	309002 12
ER colletwith seal and spray nozzles Nominal clamping Ø d 7 mm	309002 7
ER collet Nominal clamping Ø d 16 mm	309000 16
ER colletwith seal Nominal clamping Ø d 11 mm	308986 11
ER collet Nominal clamping Ø d 18 mm	308981 18
ER colletwith seal and spray nozzles Nominal clamping Ø d 11 mm	309002 11
ER collet Nominal clamping Ø d 12 mm	309000 12
ER colletwith seal and spray nozzles Nominal clamping Ø d 6 mm	309002 6
ER collet Nominal clamping Ø d 18 mm	309000 18

ER collet Nominal clamping Ø d 10 mm	308981 10
ER colletwith seal and spray nozzles Nominal clamping Ø d 3 mm	309002 3
ER collet Nominal clamping Ø d 12 mm	308981 12
ER collet Nominal clamping Ø d 11 mm	309000 11
ER collet set 8 pieces 4–16, 20 mmwith seal	309026
ER collet Nominal clamping Ø d 17 mm	309000 17
ER collet Nominal clamping Ø d 10 mm	309000 10
ER colletwith seal Nominal clamping Ø d 19 mm	308986 19
ER colletwith seal Nominal clamping Ø d 3 mm	308986 3
ER collet Nominal clamping Ø d 19 mm	308981 19
ER colletwith seal and spray nozzles Nominal clamping Ø d 18 mm	309002 18
ER collet Nominal clamping Ø d 15 mm	309000 15
ER collet Nominal clamping Ø d 20 mm	309000 20
ER colletwith seal and spray nozzles Nominal clamping Ø d 10 mm	309002 10
ER collet Nominal clamping Ø d 6 mm	309000 6
ER collet Nominal clamping Ø d 4 mm	308981 4
ER collet Nominal clamping Ø d 11 mm	308981 11
ER collet Nominal clamping Ø d 13 mm	309000 13
ER colletwith seal Nominal clamping Ø d 12 mm	308986 12
ER colletwith seal Nominal clamping Ø d 15 mm	308986 15
ER colletwith seal Nominal clamping Ø d 8 mm	308986 8
ER colletwith seal Nominal clamping Ø d 9 mm	308986 9
ER colletwith seal and spray nozzles Nominal clamping Ø d 16 mm	309002 16
ER colletwith seal and spray nozzles Nominal clamping Ø d 13 mm	309002 13
ER colletwith seal Nominal clamping Ø d 7 mm	308986 7
ER chuck key for ER collet chuck 32	309680 32

ER colletwith seal Nominal clamping Ø d 13 mm	308986 13
ER colletwith seal and spray nozzles Nominal clamping Ø d 5 mm	309002 5
ER collet Nominal clamping Ø d 9 mm	309000 9
ER collet Nominal clamping Ø d 16 mm	308981 16
ER collet Nominal clamping Ø d 8 mm	309000 8
ER colletwith seal and spray nozzles Nominal clamping Ø d 9 mm	309002 9
ER colletwith seal Nominal clamping Ø d 18 mm	308986 18
ER collet Nominal clamping Ø d 17 mm	308981 17
ER collet Nominal clamping Ø d 19 mm	309000 19
ER collet Nominal clamping Ø d 7 mm	308981 7
ER colletwith seal Nominal clamping Ø d 5 mm	308986 5
ER collet Nominal clamping Ø d 5 mm	308981 5
ER collet Nominal clamping Ø d 5 mm	309000 5
ER colletwith seal Nominal clamping Ø d 17 mm	308986 17
ER colletwith seal Nominal clamping Ø d 14 mm	308986 14
ER collet Nominal clamping Ø d 7 mm	309000 7
ER colletwith seal and spray nozzles Nominal clamping Ø d 4 mm	309002 4
ER colletwith seal and spray nozzles Nominal clamping Ø d 20 mm	309002 20
ER collet Nominal clamping Ø d 14 mm	308981 14
ER collet Nominal clamping Ø d 8 mm	308981 8
ER colletwith seal Nominal clamping Ø d 6 mm	308986 6
ER colletwith seal and spray nozzles Nominal clamping Ø d 14 mm	309002 14
ER collet Nominal clamping Ø d 13 mm	308981 13
ER collet Nominal clamping Ø d 15 mm	308981 15
ER colletwith seal and spray nozzles Nominal clamping Ø d 15 mm	309002 15

ER colletwith seal Nominal clamping Ø d 20 mm	308986 20
ER collet Nominal clamping Ø d 14 mm	309000 14