



Impact wrench 18 V, cordless impact wrench



Order data

Order number	074010 M18ONEF1DS
GTIN	4058546564179
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. With 18 FUEL™ ONEKEY™ 1 inch cordless impact wrench with snap ring, provides up to 2576 Nm of tightening torque and replaces wired, petrol and pneumatic devices. DRIVE CONTROL enables quick switching between the 4 available settings with different speeds and torques.

Advantage:

DRIVE CONTROL™.

Supplied with:

Includes 1× M18 Forge™ 12 Ah, charger, HD box.

Note:

See No. 073801 – No. 073840 for suitable batteries and chargers.

Technical description

maximum torque 1st step	1180 Nm
Power supply	Battery-powered
Battery capacity	12 Ah
maximum torque 4th setting	2576 Nm
Number of impacts 2nd stage	0 - 930 min ⁻¹
Weight	11.1 kg
Number of impacts 3rd stage	0 - 1200 min ⁻¹
maximum torque 3rd step	1966 Nm
Number of impacts 1st stage	0 - 750 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Packaging	Modular case (HD=Heavy Duty)
Tool arbor drive profile	External square drive
typical application	Heavy Duty
App link	OneKey
Number of impacts 4th setting	0 - 1440 min ⁻¹
Manufacturer's designation	M18ONEFHI-WF1DS-121C
Tool arbor size	1 in
Type of rechargeable battery	Lithium-ion
maximum screw Ø (8.8 - 12.9)	M42
Number of rechargeable batteries contained	1
maximum torque 2nd step	1254 Nm
Battery voltage	18 V
Type of product	Impact wrench