



Cordless angle grinder 18V, for 230 mm discs Ø, with battery



Order data

Order number	077135 M18FLAG230
GTIN	4058546564056
Item class	03L

Description

Version:

Cordless two-hand angle grinder Ø 230 mm. Version with a dead man's switch and restart inhibit.

The latest generation of the brushless POWERSTATE™ motor (powered by only a single 18 V / 12 Ah High Output™ battery pack)

Supplied with:

Supplied with 1 pc. 18 V / 12 Ah **FORGE™** Li-ion rechargeable battery, charger M12-18 FC, safety guard piece, AVS side handle, Fixtec quick clamping nut, 2 pcs. exchangeable dust-protection grilles, carrying case.

Technical description

Special features	Dead man's switch; FIXTEC
Battery capacity	12 Ah
Manufacturer's designation	M18FLAG230XP-DB-121C
maximum disc Ø	230 mm
maximum speed	6600 min ⁻¹
Battery voltage	18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Number of rechargeable batteries contained	1

Data sheet

maximum vibration to EN	8.7 m/s ²
Weight	5.2 kg
Type of rechargeable battery	Lithium-ion
Restart block	yes
maximum cutting depth	65 mm
Type of product	Angle grinder