

**Cordless circular saw, Type: M18-FMCS66****Order data**

Order number	078207 M18-FMCS66
GTIN	4058546564070
Item class	03L

Description**Version:**

Cordless circular saw for metal 66 mm.

- **Large metal swarf collector catches the residue created during cutting and provides the necessary clear view.**
- **Dry cutting technology permits quick, clean and burr-free metal cutting.**

Supplied with:

Includes rechargeable battery, charger, transport case.

Note:

Suitable spare rechargeable batteries and chargers can be found as from No. 073801 – 073840.
For a suitable circular saw blade see from No. 584075.

Technical description

Battery voltage	18 V
Weight	7.3 kg
maximum vibration to EN	< 2.5 m/s ²
Number of rechargeable batteries contained	1
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V

Data sheet

Saw blade bore Ø	16 mm
Battery capacity	12 Ah
maximum speed	4000 min ⁻¹
Type of rechargeable battery	Lithium-ion
Manufacturer's designation	M18-FMCS66-802C
maximum cutting depth 90°	66 mm
Packaging	Modular case (HD=Heavy Duty)
Power supply	Rechargeable battery-powered
Version	Hand-held circular saw
Saw blade Ø	203 mm
Type of product	Saw

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/078207-M18-FMCS66>