



Side lock arbor, SK 50, Clamping range \varnothing D1: 8mm



Order data

Order number	302440 8
GTIN	4250122600343
Item class	36E

Description

Version:

Internal thread for manual clamping.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Technical description

Spare clamping screw No. 30 9900	8
Thread M	M24
Overall length L	190 mm
Clamping \varnothing D ₁	8 mm
Overhang dimension A	63 mm
External \varnothing D	28 mm
Adapter	SK 50
Standard	DIN 6359
Arbor standard	DIN 2080
Concentricity	$\leq 3 \mu\text{m}$
Type of product	Side lock arbor

Accessories

Pull studForm A suitable for steep tapers 50	308600 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull studsealed suitable for steep tapers 50	308660 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Pull studForm B suitable for steep tapers 50	308640 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull studsealed, form B suitable for steep tapers 50	308620 50
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Spare clamping screw for chucks with clamping Ø D1 8 mm	309900 8