

**Battery / mains radio, Type: GPB18VH-6****Order data**

Order number	073961 GPB18VH-6
GTIN	4053423301526
Item class	03B

Description**Version:**

Sturdy site radio, splash-proof (IP54) for mains and battery operation. Powerful radio with charging function for 12V and 18V rechargeable batteries.

- **Premium sound with DAB+, FM, Bluetooth®, AUX and multi-speaker sound.**
- **Compatible with L-BOXX to easily transport the radio to any construction site.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes mains cable, 2 back-up batteries, AUX connection cable, without batteries.

Technical description

Power supply	Battery-powered
Height	336 mm
suitable battery - supplier / battery type / voltage	Bosch 18 V
suitable battery - supplier / battery type / voltage	Bosch 12 V
Type of rechargeable battery	Lithium-ion

Data sheet

Length	476 mm
IP Index of Protection	IP 54
Number of rechargeable batteries contained	0
Width	249 mm
Weight	8.2 kg
Interface	USB interface
Interface	Bluetooth® interface
Battery voltage	12 V
Battery voltage	18 V
Type of product	Radio