



Digital dial indicator with touch control and i-wi 0.0005 mm reading, Measuring range: 25mm



Order data

Order number	434325 25
GTIN	4059192066659
Item class	43A

Description

Version:

Digital dial indicator with **very large** numeric display and integrated tolerance display.

Additional analogue scale display with tolerance limits.

Hardened glass front with wear-free touch control fields, 3 PRESET values, coloured LED display depending on tolerance mode.

With **integral i-wi** radio system for easy cordless transmission of measured data to any PC.

Dynamic measurement functions (MAX / MIN / MIN-MAX): For concentricity and flatness testing or seeking the reversal point.

Function:

PRESET, tolerance, ABS (display can be set to zero without losing the reference to PRESET), factor (multiplier for measuring distance), LOCK function (button lock in menu). Data can be transmitted. IP42: Protected against water falling obliquely (dripping water) up to 15° relative to normal operating position and protected against penetration by foreign bodies with $\varnothing > 1$ mm. However, tools and wires should be kept away.

Supplied with:

1 battery No. 081560 size CR 2450.

Optional extras:

Data cable No. 498941.

i-wi radio receiver No. 498912 STICK.

Technical description

#Number of batteries contained	1
Reversible reading	0.00002 in
#Article no of the battery / rechargeable battery fitted	081560 CR2450
Reversible reading	0.0005 mm
Calibration	C1
Measurement variation E MPE (measurement range)	0.004 mm
Clamping shank Ø h6	8 mm
Gauging force	0.65 – 1.15 N
IP Index of Protection	IP 42
Power supply	Battery-powered
Loop on the back of the dial indicator	no
Standard	Works standard
Reversible reading	mm / inch
Interface	USB interface
Interface	USB interface
Interface	MAHR i-wi radio system
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Type of product	Dial indicator

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/434325-25>