

Garant

**Shrink-fit chuck extension 4.5° without length adjustment screw, L = 300 mm,
Ø d / Ø D1: 32/20mm**

**Order data**

Order number	302416 32/20
GTIN	4045197436184
Item class	31A

Description**Version:**

Bored through for internal coolant supply (IC).

Without length adjustment screw, **long**.

Application:

For use in shrink-fit chucks, hydraulic chucks, and ER collet chucks.

Note:

Maximum permissible speed 8,000 rpm.

Technical description

Shank Ø d	32 mm
Ø D ₂	27 mm
Bore Ø D ₁	20 mm
Overall length L	300 mm
Product name attribute	L = 300 mm
Type of product	Extension