



## ER collet chuck, SK 40, for ER collet size: 40



### Order data

Order number	302465 40
GTIN	4250122600114
Item class	36E

### Description

#### Application:

For clamping tools with plain shank in ER / ESX collets to ISO 15488-B.

#### Optional extras:

ER collets No. 308981 – 309040, ER sets No. 309024 – 309320, ER clamping wrenches No. 309680 – 309740.

### Technical description

Clamping range	4 - 26 mm
Spare ER clamping nut for ER collets	40
Overhang dimension A	80 mm
Thread M	M16
External Ø D	63 mm
Adapter	SK 40
Arbor standard	DIN 2080
Concentricity	≤ 3 µm
Type of product	Collet chuck

## Accessories

ER collet Nominal clamping Ø d 5 mm	308990 5
ER collet Nominal clamping Ø d 8 mm	309040 8
ER collet Nominal clamping Ø d 24 mm	309040 24
ER collet Nominal clamping Ø d 7 mm	309040 7
ER collet Nominal clamping Ø d 12 mm	309040 12
ER collet Nominal clamping Ø d 26 mm	308990 26
ER collet Nominal clamping Ø d 6 mm	308990 6
ER collet Nominal clamping Ø d 21 mm	308990 21
ER collet Nominal clamping Ø d 16 mm	308990 16
ER colletwith seal Nominal clamping Ø d 6 mm	308992 6
ER colletwith seal Nominal clamping Ø d 8 mm	308992 8
ER collet Nominal clamping Ø d 16 mm	309040 16
ER collet Nominal clamping Ø d 18 mm	309040 18
ER collet Nominal clamping Ø d 14 mm	309040 14
ER collet Nominal clamping Ø d 19 mm	308990 19
ER collet Nominal clamping Ø d 4 mm	309040 4
ER collet Nominal clamping Ø d 15 mm	309040 15
ER collet Nominal clamping Ø d 14 mm	308990 14
ER collet Nominal clamping Ø d 24 mm	308990 24
ER collet Nominal clamping Ø d 15 mm	308990 15
ER collet Nominal clamping Ø d 22 mm	308990 22
ER colletwith seal Nominal clamping Ø d 18 mm	308992 18
ER colletwith seal Nominal clamping Ø d 10 mm	308992 10
ER collet Nominal clamping Ø d 11 mm	309040 11
ER colletwith seal Nominal clamping Ø d 20 mm	308992 20
ER chuck key for ER collet chuck 40	309680 40
ER colletwith seal Nominal clamping Ø d 14 mm	308992 14

ER collet Nominal clamping Ø d 19 mm	309040 19
ER collet Nominal clamping Ø d 5 mm	309040 5
ER collet Nominal clamping Ø d 23 mm	308990 23
ER collet Nominal clamping Ø d 9 mm	308990 9
ER collet Nominal clamping Ø d 17 mm	309040 17
ER collet Nominal clamping Ø d 11 mm	308990 11
ER collet Nominal clamping Ø d 20 mm	309040 20
ER collet Nominal clamping Ø d 26 mm	309040 26
ER colletwith seal Nominal clamping Ø d 12 mm	308992 12
ER collet Nominal clamping Ø d 13 mm	308990 13
ER collet Nominal clamping Ø d 21 mm	309040 21
ER collet Nominal clamping Ø d 10 mm	309040 10
ER collet Nominal clamping Ø d 9 mm	309040 9
ER collet set 23 pieces 4–26 mm	309028
ER colletwith seal Nominal clamping Ø d 22 mm	308992 22
ER collet Nominal clamping Ø d 7 mm	308990 7
ER collet Nominal clamping Ø d 25 mm	309040 25
ER collet Nominal clamping Ø d 6 mm	309040 6
ER collet Nominal clamping Ø d 20 mm	308990 20
ER collet Nominal clamping Ø d 17 mm	308990 17
ER collet Nominal clamping Ø d 25 mm	308990 25
ER collet Nominal clamping Ø d 13 mm	309040 13
ER colletwith seal Nominal clamping Ø d 16 mm	308992 16
ER collet Nominal clamping Ø d 12 mm	308990 12
ER collet Nominal clamping Ø d 23 mm	309040 23
ER collet Nominal clamping Ø d 10 mm	308990 10
ER collet Nominal clamping Ø d 8 mm	308990 8
ER collet Nominal clamping Ø d 22 mm	309040 22
ER colletwith seal Nominal clamping Ø d 25 mm	308992 25

ER collet Nominal clamping Ø d 18 mm	308990 18
ER collet Nominal clamping Ø d 4 mm	308990 4