



Surface brush Steel wire 0.30 mm, Brush Ø D1: 50mm



Order data

Order number	574750 50
GTIN	4017359005576
Item class	57L

Description

Version:

Area brushes with **shank Ø 6 mm.**

Application:

In straight die grinders, flexible shafts or on stationary machines. For cleaning and deburring small to medium-sized areas.

Technical description

Shank Ø D _s	6 mm
Bristle thickness	0.3 mm
Length of brush section H ₁	28 mm
maximum speed	10500 min ⁻¹
Brush Ø D ₁	50 mm
Type of product	End brush