



Digital internal quick measuring device with data output, Measuring range: 85-100mm



Order data

Order number	428933 85-100
GTIN	4059192065409
Item class	43A

Description

Version:

3-point internal micrometers / internal quick measuring devices with connection thread to easily change the measuring heads. Self-centring micrometer head from 12 mm with carbide measuring jaws. From 40 mm the micrometer head is of aluminium, to save weight. **From 12 mm for measuring down to the bottom of the hole.**

Internal quick measuring devices with lever retraction over the entire measuring range. Large rotating (270°) touch display with practical measuring functions, e.g. 3 PRESET, tolerance display via 3 coloured LEDs and symbols in the display, ABS.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Extension No. 428950, data cable No. 498941, setting rings No. 484030, clamping plate for outside micrometer stand No. 428951.

Technical description

Error limit	0.005 mm
Standard measuring depth	97 mm
Scale divisions	0.001 mm
IP Index of Protection	IP 65

Data sheet

Measuring range	85 - 100 mm
Dimension a	0.5 mm
Power supply	Battery-powered
#Article no of the battery / rechargeable battery fitted	081560 CR2032
#Number of batteries contained	1
Standard	DIN 863
Reversible reading	mm / inch
Interface	USB interface
Interface	USB interface
Interface	MAHR i-wi radio system
Measured value saving	MAHR reference-lock system
Preset function	yes
Measurement technology	digital
Packaging	sturdy box
Calibration	B6
Type of product	3-point bore gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/428933-85-100>