

**Compact grinding disc U-Edge Pro (ZA), Ø 125 mm, Grit: 60****Order data**

Order number	566315 60
GTIN	4027497236589
Item class	53L

Technical description

Disc Ø	125 mm
Bore Ø	22.23 mm
Grit	60
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap wheel

User data

Data sheet

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
dry	suitable		