

**Drill/driver, cordless drill/driver****Order data**

Order number	070215 M12BLDDRC2
GTIN	4058546568504
Item class	03L

Description**Version:**

MILWAUKEE – Cordless power drill Powerful cordless 2-speed drill / driver, reversible. REDLITHIUM™ rechargeable batteries with **single-cell monitoring** and **charge status display**. Sturdy **metal gearbox** for long working life. **FIXTEC metal quick-clamping drill chuck** with spindle lock. LED illumination of the working area. Handle with Softgrip coating for comfortable use.

- **Extremely compact design with a length of only 132 mm, perfect for use in confined spaces.**
- **Mechanical slip clutch with 13 torque levels.**

Supplied with:

Supplied with 2 pcs. 12 V / 2.0 Ah Li-ion batteries, charger, belt clip, HD box.

Note:

See No. 073816, No. 073827 and No. 073840 ff. for suitable replacement batteries and chargers.

Technical description

Manufacturer's designation	M12 BLDDRC-202C
Type of rechargeable battery	Lithium-ion

Data sheet

suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Suitable for material	Wood
maximum twist drill size Ø in wood	22 mm
maximum twist drill size Ø in steel	10 mm
Power supply	Mains operated
Motor design	Brushless motor
maximum speed 2nd speed	1550 min ⁻¹
maximum torque hard	40 Nm
Quick-clamping chuck range	1.5 - 10 mm
Battery voltage	12 V
typical application	Medium
Battery capacity	2 Ah
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN	<2.5 m/s ²
Number of rechargeable batteries contained	2
maximum speed 1st speed	0 - 470 min ⁻¹
Weight	2.8 kg
Type of product	Drill/driver