

**Cordless pipe cutter, Type: 4933498374****Order data**

Order number	078218 4933498374
GTIN	4058546522438
Item class	03L

Description**Version:**

Compact cordless pipe cutter with stainless cutting head. **Automatic adaptation** to the pipe Ø. Minimum wall distance 43 mm. **Suitable for stainless steel, C-steel and copper pipes.** The viewing window on the cutting mechanism and the built-in lighting allow the user to cut the pipe precisely.

Supplied with:

Delivered in a box, **without** rechargeable battery and **without** charger.

Note:

See No. 073801 – No. 073840 for suitable batteries and chargers.

Technical description

Weight	3 kg
Power supply	Battery-powered
Number of rechargeable batteries contained	0
maximum vibration to EN	<2.5 m/s ²
Type of rechargeable battery	Lithium-ion
Speed range	0 - 330 min ⁻¹
maximum pipe Ø copper	35 - 54 mm

Data sheet

Battery voltage	12 V
maximum pipe Ø stainless steel	35 - 54 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Type of product	Pipe cutters