



## Cordless angle grinder 18V, for 125 mm discs Ø, with battery, with soft start and restart inhibit, in a case



### Order data

Order number	077140 4933493416
GTIN	4058546482879
Item class	03L

### Description

#### Version:

18 V / 5.0 Ah FUEL™ Milwaukee cordless angle grinder:

- **long-life brushless motor, spindle locking, quick adjustment of the safety guard.**
- **Integral FIXTEC quick-release system for changing discs without using tools.**

M18™ HIGH OUTPUT™ cordless angle grinder with a diameter of 125 mm and a power equivalent to that of a 1750 W grinder.

#### Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

### Technical description

Number of rechargeable batteries contained	1
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum vibration to EN	3.4 m/s <sup>2</sup>
maximum disc Ø	125 mm
Restart block	yes
Type of rechargeable battery	Lithium-ion
Overload protection	yes
Kick-back stop	yes

## Data sheet

Manufacturer's designation	M18FHSAG125XB2-802X
Weight	3.5 kg
maximum cutting depth	33 mm
Battery capacity	8 Ah
Battery voltage	18 V
Dead man's circuit	no
maximum speed	9000 min <sup>-1</sup>
Soft start	yes
Type of product	Angle grinder