

WEKEM®**Teflon sealing tape, 12 m, Type: GOLD****Order data**

Order number	083319 GOLD
GTIN	4260205360040
Item class	08G

Description**Version:**

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves. Particularly strong, leak-proof, resilient Teflon strip of the highest quality, for all types of threads. Suitable for propane, butane, natural gas, benzene, and fuels. Temperature range -240 to $+260$ °C.

Application:

Depending on the medium, pipework and size of the thread, for use up to approx. 100 bar (individual tests are necessary), at 200°C to max. 16 bar.

Note:

Before applying sealant, clean the threads with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Thickness	0.1 mm
-----------	--------

Width	12 mm
for thread types	All
Manufacturer's designation	GT
Working life after date of manufacture	60 mo
Length	12 m
Storage temperature	20 °C
Colour	yellow
Operating temperature range	-240 - 260 °C
Chemical basis	Polytetrafluorethylene (PTFE)
Characteristics	does not stick
Characteristics	non-flammable
Characteristics	does not become brittle
Product name attribute	12 m
Type of product	Sealing strip