

**Pair of gloves uvex Bamboo TwinFlex® D SG, Glove size: 8****Order data**

Order number	094267 8
GTIN	4048612139196
Item class	04W

Description**Version:**

Glove made from patented **Bamboo TwinFlex® technology**. Fine 18-gauge knitting technology combined with high cut protection level D. The **thin SoftGrip coating** offers excellent grip and high abrasion resistance. Certified to Oeko-Tex 100, touchscreen compatibility and resistant to contact heat up to 100 °C.

Application:

Suitable for dry and slightly damp working conditions.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. The model is suitable for contact heat up to +100 °C in accordance with EN 407.

Technical description

Glove characteristics	Suitable for touch screens
Knitted technology	18G
Clothing standard	Oeko-Tex Standard 100

Data sheet

EN 388	3X31D
EN 407	X1XXXX
Backing material	Bamboo viscose, HPPE, steel, PA, elastane
Coating	SoftGrip foam
Scope of application	All-round
Colour	green
Standard	EN 407
Contact heat up to	100 °C
Application	reusable
Cut protection class	D
Type of product	Cut-resistant gloves