

**Pair of gloves uvex Bamboo TwinFlex® D SG, Glove size: 10****Order data**

|              |               |
|--------------|---------------|
| Order number | 094267 10     |
| GTIN         | 4048612139257 |
| Item class   | 04W           |

**Description****Version:**

Glove made from patented **Bamboo TwinFlex® technology**. Fine 18-gauge knitting technology combined with high cut protection level D. The **thin SoftGrip coating** offers excellent grip and high abrasion resistance. Certified to Oeko-Tex 100, touchscreen compatibility and resistant to contact heat up to 100 °C.

**Application:**

Suitable for dry and slightly damp working conditions.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. The model is suitable for contact heat up to +100 °C in accordance with EN 407.

**Technical description**

|                       |                            |
|-----------------------|----------------------------|
| Glove characteristics | Suitable for touch screens |
| Knitted technology    | 18G                        |
| Clothing standard     | Oeko-Tex Standard 100      |

## Data sheet

|                      |                                           |
|----------------------|-------------------------------------------|
| EN 388               | 3X31D                                     |
| EN 407               | X1XXXX                                    |
| Backing material     | Bamboo viscose, HPPE, steel, PA, elastane |
| Coating              | SoftGrip foam                             |
| Scope of application | All-round                                 |
| Colour               | green                                     |
| Standard             | EN 407                                    |
| Contact heat up to   | 100 °C                                    |
| Application          | reusable                                  |
| Cut protection class | D                                         |
| Type of product      | Cut-resistant gloves                      |