

**LED torch with rechargeable battery, Type: P4R****Order data**

Order number	081398 P4R
GTIN	4058205037013
Item class	04B

Description**Version:**

Ledlenser is one of the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head. Dual Power – operation with rechargeable battery or standard batteries.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes rechargeable battery.

Technical description

Overall length	142 mm
Illumination time stage 3	13 h
IP Index of Protection	IP 54
Illumination	300 lm
Number of rechargeable batteries contained	1
Weight	57 g
Illumination step 3	25 lm
Head Ø	15 mm
Type of rechargeable battery	Lithium-ion

Data sheet

Illumination time stage 2	3 h
Illumination time	1.5 h
Illumination step 2	100 lm
Type of product	Torch