

**LED torch Pro with rechargeable battery, Type: P7R-PRO****Order data**

Order number	081399 P7R-PRO
GTIN	4058205037136
Item class	04B

Description**Version:**

Ledlenser is one of the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All lamps are equipped with focussable lamp head. Intuitive operation via rotary dial.

Supplied with:

Includes rechargeable battery, charging station, wrist strap, protective elements.

Technical description

Illumination time stage 3	60 h
Illumination	1000 lm
Light current boost	2000 lm
Weight	223 g
Overall length	170 mm
Illumination time stage 2	5 h
Illumination time	2.5 h
Illumination time boost	10 s
Number of rechargeable batteries contained	1
Illumination step 2	450 lm

Data sheet

Head Ø	42 mm
Illumination step 3	25 lm
IP Index of Protection	IP 68
Type of rechargeable battery	Lithium-ion
Type of product	Torch