

**Pair of gloves uvex phynomic C XG ESD, Glove size: 10****Order data**

Order number	094462 10
GTIN	4048612120279
Item class	04W

Description**Version:**

uvex phynomic C XG ESD. The dexterous glove with cut protection level C fits like a second skin. Good grip in wet and oily working conditions. Certified to Oeko-Tex 100 and with touchscreen compatibility. Suitable for contact with food and for ESD workplaces according to EN 16350.

Standard:

EN 388; EN ISO 21420

Note:

Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages. Not suitable for working on live cables or for protection against electric shock - they protect only the product.

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove characteristics	Suitable for touch screens
Glove characteristics	Levnedsmiddelcertificering
Glove characteristics	Suitable for touch screens

Data sheet

electrostatic characteristic	ESD tested according to EN 16350
Clothing standard	Oeko-Tex Standard 100
EN 388	3X42C
Backing material	HPPE, fibreglass, PA, elastane, carbon
Coating	Aqua polymer Xtra Grip foam
Coating variant	The palms of the hands
Scope of application	All-round
Colour	blue / black
Weight	58 g
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves