

WEKEM®
Teflon sealing tape, 12 m, Type: FINE

Order data

Order number	083319 FINE
GTIN	4260205360019
Item class	08G

Description
Version:

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

Application:

PTFE thread sealing tape FRp can be used up to 3/8 inch for: Air, nitrogen, gas up to max. 5 bar, liquid gas, tap water up to max. 16 bar can be used up to 100 bar (at 200°C up to max. 16 bar).

Note:

Before applying sealant, clean the threads with general-purpose cleaner No. 083391 and No. 083392.

Technical description

Thickness	0.1 mm
Manufacturer's designation	FRp
for thread types	fine

Width	12 mm
Operating temperature range	-240 °C
Length	12 m
Colour	white
Storage temperature	20 °C
Working life after date of manufacture	60 mo
Chemical basis	Polytetrafluorethylene (PTFE)
Characteristics	does not become brittle
Characteristics	non-flammable
Characteristics	does not stick
Product name attribute	12 m
Type of product	Sealing strip