

**D-bits, Solid carbide, D×Length: 4X63mm****Order data**

Order number	295050 4X63
GTIN	4045197188274
Item class	22E

Description**Version:**

Solid carbide. D-bits with straight cutting edge. Precision ground with maximum run-out error 0.005 mm. Half section pre-ground. **Shank tolerance up to diameter 8 mm = h7.**

Application:

For engraving and copying in tool, mould, and die making.

Technical description

Length	63 mm
Ø D	4 mm
Cutter length	4 mm
Tool material	Solid carbide
Type of product	Tool blank