



Self-levelling cross-hair laser LINO, Type: L6G

Order data

Order number	468486 L6G
GTIN	7640110699942
Item class	47C

Description

Version:

Robust, ergonomic plastic casing; proof against dust and splashed water. **With green laser lines for optimum visibility. Up to 400% better visibility than red laser lines.**

Self-levelling multi-mains laser with 3x 360° laser lines. One horizontal and two vertical 360° laser lines. Laser lines thin, sharp and clearly visible. Laser power can be set in 3 stages for better visibility or longer operating time. Self-levelling over long distances in the event of inclined positions. Time saving by easy setting up of the zero point. Fixed zero point thanks to integral base. Simple and precise alignment of the laser lines by $\pm 10^\circ$. Memory function of personal settings. Dust-proof and splash-proof. The triple power-supply concept permits uninterrupted work. Can optionally be operated with Li-ion battery, AA batteries or power supply unit.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Li-ion battery, charger with mains adapter, battery holder, laser target board, magnetic adapter TWIST 250, wall adapter UAL 130, fall protection rope, case.

Technical description

Weight	530 g
Type of rechargeable battery	Lithium-ion
Power supply	Mains-powered
Power supply	Battery-powered
Power supply	Mains operated
Levelling range	± 4 degrees
Diameter with receiver	140 m

Data sheet

Height	110 mm
IP Index of Protection	IP 54
Depth	100 mm
Width	60 mm
Series	LINO
Working time	11 h
Threaded socket for stand	1/4 UNC in
Range with receiver	70 m
Colour of the laser	green
Error limit	± 0.2 mm/m
Number of rechargeable batteries contained	1
Range	35 m
Type of product	Cross laser