



TwinGrip® front gripping pliers chemically blacked, overall length: 150mm



Order data

Order number	705991 150
GTIN	4003773089353
Item class	73F

Description

Version:

Special, extra slim head shape for use in tight spaces. **Box joint** (= double guidance). Designed to prevent fingers being trapped. Fine adjustment at intervals by means of a spring-loaded pushbutton, for precisely adapting the width. Front gripping and side gripping function. Jaws chemically greyed, polished head, teeth additionally induction hardened (approx. 61 HRC). Plastic coated handles.

Application:

Reliable frontal gripping of even flat workpieces due to three-point system. Gripping, tightening and releasing of even hardened screw heads as well as worn bolts and screws.

Material:

Chrome vanadium electro-steel, drop forged.

Technical description

overall length	150 mm
Jaw width	9 mm
Jaw length	21 mm
Series	TwinGrip®
Hexagon across flats	16 mm
Number of fine adjustment steps	3
Jaw capacity for pipes	5/8 in
Type of jaws	3-point system

Data sheet

Handle	plastic coated
Material	Chrome vanadium electro-steel
Type of product	Pipe pliers