

**Heavy-duty side cutter, chrome-plated, with grips, overall length: 200mm****Order data**

Order number	723101 200
GTIN	4003773035367
Item class	73F

Description**Version:**

Heavy-duty head with additionally induction hardened cutting edges (approx. 64 HRC). Laid-on joint. High cutting performance due to optimum leverage.

Pliers chrome-plated, handles with multi-component sleeves and KNIPEXtend interface.

Application:

For all types of wire (long working life even with hard wire). Heavy duty for the most demanding applications.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	4.2 mm
Cutting capacity hard wire up to Ø	3 mm
Cutting capacity piano wire up to Ø	2.5 mm
overall length	200 mm
Standard	DIN ISO 5749
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)

Data sheet

Material	Chrome vanadium electro-steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers