

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 12/11mm


Order data

Order number	260919 12/11
GTIN	4045197653406
Item class	21T

Technical description

ISO code toolholder	E12M STFCL/L11
suitable indexable insert	TC.. 1102..
Centre offset L_3	8 mm
Minimum pre-drill $\varnothing D_{\min}$	15 mm
Insert size	11 mm
Head length L_1	20 mm
Pack of insert screws	269028 7
Overall length L	150 mm
Clamping height L_2	11.5 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500