

**Ultrasonic cleaning unit Elmasonic Xtra, Type: 4****Order data**

Order number	082006 4
GTIN	4250004112506
Item class	04S

Description**Version:**

Powerful ultrasonic cleaning by the Elmasonic xtra series for heavy-duty applications.

- **Greater ultrasonic effect due to automatic dynamic function.**
- **Selectable Eco mode for gentle cleaning and energy savings.**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Individual timer and temperature control.**
- **Clearly arranged, splash-proof control panel.**
- **Automatic safety shutdown.**

Note:

Further sizes and types on request. The suitable component basket can be found under No. 082101. Ultrasonic cleaning agent and anti-corrosion agent can be found under No. 088015 – No. 088019.

Technical description

Item length	435 mm
Item width	215 mm
Manufacturer's designation	Xtra 40
Weight	6.8 kg
Length of component basket	195 mm
Volume	5 l

Data sheet

Maximum ultrasonic power	560 W
Recommended working volume	4 l
Width of component basket	105 mm
Heating power	400 W
Nominal voltage	220 - 240 V
Cleaning bath height	150 mm
Type of product	Ultrasonic cleaning unit